

DCS Series
M51 Isolated
Analog Option
Programming Manual

Sorensen Power Supplies
Elgar Electronics Corporation
9250 Brown Deer Road
San Diego, CA 92121-2294
1-800-73ELGAR (1-800-733-5427)
Tel: (858) 450-0085
Fax: (858) 458-0267
Email: sales@elgar.com
www.elgar.com

©2002 by Elgar Electronics Corporation

This document contains information proprietary to Elgar Electronics Corporation. The information contained herein is not to be duplicated or transferred in any manner without prior written permission from Elgar Electronics Corporation.

CONTENTS

SECTION 1 DESCRIPTION AND SPECIFICATIONS.....	1-1
1.1 Introduction.....	1-1
1.2 Specifications	1-1
SECTION 2 INSTALLATION AND OPERATING INSTRUCTIONS.....	2-1
2.1 Programming Connection.....	2-1
2.2 Programming Mode	2-1
2.3 Operation.....	2-2
2.4 Calibration	2-2
SECTION 3 THEORY OF OPERATION.....	3-1
3.1 General.....	3-1
3.2 Isolation Amplifier	3-1
3.3 Isolated Power Supply.....	3-1
SECTION 4 SCHEMATICS	4-1
TABLES AND FIGURES	
Table 2-1 Mode Select Switch	2-1
Figure 2-1 Connector J1	2-1

This page intentionally left blank.

SECTION 1 DESCRIPTION AND SPECIFICATIONS

1.1 Introduction

The M51 isolated interface allows complete remote programming control of either the power supply output voltage or current using analog program signals, that may be biased at any potential relative to the power supply return line (within the maximum voltage differential specification). The program mode is selected by setting 5 DIP switches located on the back panel, and the program input port is a standard 15 pin female D-SUB connector.

1.2 Specifications

Maximum Voltage Differential:

Between program input / power supply return	600VDC
---	--------

Remote Programming Control Coefficient: ($\pm 1\%$)

Output Voltage	(0-10V pgm, Switch Select)	1V/10% of V_o
	(0-5V pgm, Switch Select)	1V/20% of V_o
	(0-400mV pgm, Switch Select)	0.1V/25% of V_o
Output Current	(0-10V pgm, Switch Select)	1V/10% of I_o
	(0-5V pgm, Switch Select)	1V/20% of I_o
	(0-400mV pgm, Switch Select)	0.1V/25% of I_o

(Program scales can be adjusted within $\pm 5\%$ of the nominal value, if required, see Section 2.4 Calibration.)

Input Impedance: 20K

Program Connector:

15 pin D-sub female - mating part 15 pin D-sub male
(typical part AMP 747908)

This page intentionally left blank.

SECTION 2

INSTALLATION AND OPERATING INSTRUCTIONS

2.1 Programming Connection

Connect the remote program signal line to the input connector (J1) as shown below. Check that signal polarity is correct (+ to J1 pin 7, – to J1 pin 6). Wiring for the program line should be either a twisted pair, or a shielded pair, with the shield tied to the power supply chassis.




Figure 2-1 Connector J1

2.2 Programming Mode

The interface board may be set to remotely program either the output voltage or the output current of the power supply, or it may be set for standard local front panel control. The input can also be configured to accept either a 0-10V, 0-5V or 0-400mV control signal.

The operating mode of the interface is set with the 8-position DIP (SW1) located on the rear panel of the unit. The switch settings are as follows:

MODE	SW1-1	SW1-2	SW1-3	SW1-7	SW1-8
Local Control (no programming)	OFF	x	x	x	x
Output Current Pgm 0-400mV	ON	ON	OFF	OFF	OFF
0-5V	ON	ON	OFF	ON	OFF
0-10V	ON	ON	OFF	OFF	ON
Output Voltage Pgm 0-400mV	ON	OFF	ON	OFF	OFF
0-5V	ON	OFF	ON	ON	OFF
0-10V	ON	OFF	ON	OFF	ON

(x = don't care, SW1-4 to SW1-6 are always off)

Table 2-1 Mode Select Switch

2.3 Operation

After appropriate programming mode has been selected, and the external programming voltage source has been connected, the output of the power supply may be varied by adjusting the programming voltage.

**CAUTION!**

Never allow the power supply output voltage or current to exceed the rated maximum.

2.4 Calibration

If the program range or offset should require calibration, adjustments may be made via multi turn trimpots located on the M51 isolated interface control board. (Remove cover of power supply for access).

<u>Designation</u>	<u>Parameter Affected</u>
R11	Program Offset Adjust
R8	Program Range Adjust

SECTION 3

THEORY OF OPERATION

3.1 General

The M51 interface board consists of two functional blocks, the isolation amplifier with input buffer amplifier and associated switching circuitry, and the isolated power supply, which provides power to the input side of the isolation amplifier.

Refer to Section 4 for a link to the Elgar website to view the detailed schematic diagram for the following circuit description.

3.2 Isolation Amplifier

The isolation amplifier U1, has a capacitively isolated input stage, which prevents any D.C. currents from flowing between the programming source, and the power supply. It has a fixed overall unity gain, which allows for simple interfacing of the external program signal and the internal control points. U3 amplifies and buffers the input signal, with R8 and R11 providing range and offset adjustment points, while R7, R6 and R5 in conjunction with SW1-7 and 8 set the appropriate program scale.

Quad analog switch, U2, connects the output of the amplifier to either the voltage program line (J2-9) or the current program line (J2-8), depending on the setting of SW1-2 and SW1-3 (see Table 2-1 for settings). The control line that is not being programmed is connected to the R4, R3 voltage divider, which provides a fixed full scale (5V) program signal. SW1-1 sets the power supply in the remote control mode by pulling pin J2-4 low. In this way the single isolation amplifier can be used to program either the output voltage or current, while the other non-programmed line is held at the full scale level, independent of where the front panel control knobs are set.

3.3 Isolated Power Supply

The isolated power supply is required to provide +12V and -5V to the input side of the isolation amplifier, while maintaining electrical isolation between this section of the M51 board and the DCS unit output.

The power supply is a low power flyback type circuit, controlled by U5, a 100kHz current mode pulse width modulator (PWM). This PWM controls the on time of the switching transistor Q1, a

N-channel MOSFET, which controls the power delivered to the secondary T1, the isolation transformer. The transformer winding voltage is sensed at the control circuit by rectifying and filtering the output of the control winding at T1 pin 9 and 2. This voltage is divided by R13 and 14 to approximately 2.5V, the same level as the internal reference in the PWM. The on time of Q1 is controlled to maintain this sensed voltage at 2.5V, which also keeps the main secondaries at pin 6, 7 and 8 regulated.

The main secondaries are rectified and filtered to provide approximately $\pm 15V$ to the post regulators U3 and U4. U3 provides a fixed 12V to the input stage of U1, while U4 provides a fixed -5V. The 14-20V input to the isolated supply is from the raw auxiliary supply on the main DCS unit, while the output stage of the isolation amplifier is driven by the +12V and -5V supply on the main DCS control board.

SECTION 4 SCHEMATICS

Please click on the link below to access assembly drawings, schematics, bills of materials, and latest updates to this manual. To view these documents, you must be connected to the Internet.

[DRAWINGS](#)

This page intentionally left blank.